


52103105	DATA SHEET	
Valid from: 24.11.2023	SKINDICHT® BL-M with O-Ring	

SKINDICHT® BL-M blind plugs are used wherever already existing housing holes are not yet required or no longer required. Our blind plug model is equipped with a screwing slit, which makes installation significantly easier. The SKINDICHT® BL-M is qualified for using by machine-, apparatus construction and drives.



Components:

Blind plug	Brass, nickel-plated Brass lead free, nickel-plated
O-Ring	NBR

Technical features:

Connecting thread	M12x1,5 up to M75 x1,5 acc. to EN 60423
Protection class	IP68 (10bar/30min), acc. to EN 60529 Type 1 and Type 12, acc. to UL50E (except size M75x1,5)
Temperature range	-20 °C up to +100 °C


Approbation:




Norm references:



Creator: T. Dvoulety /PDP Released: DAMU1/PDP	Document: DB52103105EN Version: 09	Page 1 of 2
--	---------------------------------------	-------------

52103105	DATA SHEET	
Valid from: 24.11.2023	SKINDICHT® BL-M with O-Ring	

SKINDICHT® BL-M



M	Ø A [mm]	C [mm]	D [mm]	O-Ring [mm]	Article No.	
					Brass	Brass lead free
M12x1,5	14	7,5	5	9 x 2	52103105	52103105LF
M16x1,5	18	8	5	13 x 2	52103115	52103115LF
M20x1,5	22	9,5	6	17 x 2	52103125	52103125LF
M25x1,5	28	11	7	22 x 2	52103135	52103135LF
M32x1,5	35	12	8	28 x 2	52103145	52103145LF
M40x1,5	44	13	9	36 x 2	52103155	52103155LF
M50x1,5	54	15	9	46 x 2	52103165	52103165LF
M63x1,5	70	16	10	57 x 2	52103175	52103175LF
M75x1,5	80	17	11	65 x 2	52103195	52103195LF

For more information, please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: T. Dvoulety /PDP Released: DAMU1/PDP	Document: DB52103105EN Version: 09	Page 2 of 2
--	---------------------------------------	-------------