


7433501070	<b>DATA SHEET</b>	
Valid from: 19.02.2026	<b>EPIC® MC03C2LSAB22CK20</b>	

## Description

- Sensor/actuator PVC-cable, unshielded
- M12 Connector, A-coding, 3 Pin



## Product variations

Article no.	Article description	P1 - cable end	P2 - cable end	Length (mm)
7433501070	EPIC® MC03C2LSAB22CK20	coupling, straight	Open end	2000 +100/-20
7433501071	EPIC® MC03C2LSAB22CK50	coupling, straight	Open end	5000 +150/-30
7433502689	EPIC® MC03C3LSAB22CK20	connector, straight	coupling, straight	2000 +100/-20

Other lengths are available on request.

## Connector, general characteristics

Coding	A-Coding
Number of poles / pins	3
Product standard	IEC 61076-2-101 (2024)
Shielded	No
Protection class	IP 67
Pollution degree	3
Ambient temperature (connected)	-25 up to +80°C (Flexible) -40 up to +80°C (Fixed)
Plugging cycles	≥ 100
Tightening torque	Recommended:0.4 Nm Max:0.8 Nm


## Connector, electrical properties

Rated voltage	250V AC OR DC
Rated surge voltage	2500 V
Rated current	4 A
Insulation resistance	≥ 100 MΩ
Contact resistance of connector	≤ 5 mΩ

## Connector, materials

Contacts- Male connector	Brass, gold plated
Contacts- Female connector	Phosphor, gold plated
Insert	PA66+GF
Overmold	TPU/ Black
Threaded part	Brass, nickel plated
Sealing	FKM

Creator: Drake Long / PDCF Released: SOLI1 / PDCF	Document: DB7433501070EN Version: 00	Page 1 of 3
--	---	-------------

7433501070	<b>DATA SHEET</b>	
Valid from: 19.02.2026	<b>EPIC® MC03C2LSAB22CK20</b>	

### Cable, general characteristics

AWM style	UL2464
Conductor cross-section	22 AWG (0.34mm <sup>2</sup> )
Number of conductors	3 (1. Brown, 2. Blue, 3. Black)
Core outer diameter	1.25 ±0.1mm
Jacket outer diameter	4.4±0.2mm
Cable weight	31 ± 3 kg/km
Temperature rating	VDE: -40 up to +80°C(Fixed) VDE: -5 up to +70°C(Fixed)
Flame resistance	Flame retardant acc .to IEC60332-1-2 UL: FT1 and VW1 CSA: FT1
Halogen-free	No
Oil resistance	No



### Cable, electrical properties

Rated voltage	300 V
Conductor resistance	MAX 57 Ω/km at 20°C
Dielectric strength	2000V / min.


### Cable, materials

Conductor	Bare copper
Conductor insulation	PVC
Jacket	PVC, Black


**Drawings**



P1(male)	Wire list	P2(female)
PIN 1	Brown (AWG 22)	PIN 1
PIN 3	Blue (AWG 22)	PIN 3
PIN 4	Black (AWG 22)	PIN 4



**Cross section**



**Remark**

Photographs are not to scale and do not represent detailed images of the respective products.