# Valid from: DATA SHEET

## **EPIC® POWERLOCK F6 S**



## Description

14.01.2019

- Single-pin circular connector for mobile power distribution, electro motors and generators
- Resistant to mechanical influences in harsh environmental conditions
- Connectors in harmonised colours according to European standards
- Every colour has a different coding to prevent incorrect plugging



#### **General Characteristics**

Series F6 S

Version coupling connector, drain for screw contact

Rated voltage (V) 1000 V Rated impulse voltage 8 kV

Rated current (A) max. crimp 400 A

Contacts Screw termination: silver-plated brass

Number of contacts

Termination methods Screw termination: 50 - 120 mm<sup>2</sup>

Protection IP 67 (maximum, dependant on cable gland used)

IP 20 (unmated)

Cycle of mechanical operation 500

Temperature range -25°C to +125°C

Degree of soiling 3

## **Product Variations**

| Article- Number       | Article                        | М                | Pin configuration |
|-----------------------|--------------------------------|------------------|-------------------|
| Type POWERLOCK F6     | , coupling connector, drain fo | or screw contact |                   |
| 44420262              | POWERLOCK F6 PE/GN             | 40               | PE, Green         |
| 44420263              | POWERLOCK F6 N/BL              | 40               | N, Blue           |
| 44420264              | POWERLOCK F6 L1/BN             | 40               | L1, Brown         |
| 44420265              | POWERLOCK F6 L2/BK             | 40               | L2, Black         |
| 44420266              | POWERLOCK F6 L3/GY             | 40               | L3, Grey          |
| L1/red for direct cur | rent applications in conjuncti | on with L2/black |                   |
| 44420301              | POWERLOCK F6 L1/RD             | 40               | L1, Red           |

## **Materials and Surfaces**

Housing PBT Contact retention pin PA


**Approvals** 

VDE-Approval, VDE-REG.-No. D042

| Creator: STKU3/PDP  | Document: DB44420262EN | Daga 1 of 4 |
|---------------------|------------------------|-------------|
| Released: IVSE1/PDP | Version: 03            | Page 1 of 4 |

| 44420262                  | DATA SHEET           | & LADD       |
|---------------------------|----------------------|--------------|
| Valid from:<br>14.01.2019 | EPIC® POWERLOCK F6 S | <b>WLAPP</b> |

## **Technical Drawings**



| Creator: STKU3/PDP  | Document: DB44420262EN | Dogo 2 of 4 |
|---------------------|------------------------|-------------|
| Released: IVSE1/PDP | Version: 03            | Page 2 of 4 |

## 44420262


## **DATA SHEET**

Valid from: 14.01.2019

**EPIC® POWERLOCK F6 S** 



## **System description**



|        | Line connector | Panel mount connector | Crimp contact | Screw contact                           |
|--------|----------------|-----------------------|---------------|---|
| Source | D6             | A6                    |               | 160 0 m                                 |
| Drain  | F6             | A1                    |               | Sign Sign Sign Sign Sign Sign Sign Sign |

Step 1) Selection of housings:

Step 2) Selection of SKINTOP® cable gland M40 for the housing (only cable connectors):

e.g. 3111250 (black), 53111450 (light grey), 53111050 (silver grey)

Step 3) Decision:

400 A / max. 120mm<sup>2</sup>

-> Screw contacts

660 A / max. 240mm<sup>2</sup> -> Crimp contacts

! Screw and crimp contacts are not allowed to be mixed!

Step 4) Selection of contacts:

Screw contacts with reduction sleeve (with 120mm<sup>2</sup> not necessary)

|        | 50 mm <sup>2</sup> | 70 mm²     | 95 mm²     | 120 mm <sup>2</sup> |
|--------|--------------------|------------|------------|---------------------|
| Source | 44420237 &         | 44420237 & | 44420237 & | 44420237            |
|        | 44420247           | 44420246   | 44420245   |                     |
|        |                    |            |            |                     |
| Drain  | 44420232 &         | 44420232 & | 44420232 & | 44420232            |
|        | 44420247           | 44420246   | 44420245   |                     |
|        |                    |            |            |                     |

## Contacts with M12 thread (for cable lug Ø12 mm)

|        | M12-thread 660 A | M12-thread 400 A |
|--------|------------------|------------------|
| Source |                  |                  |
|        | 44420261         | 44420242         |
| Drain  | 44420260         | 44420241         |

Tightening torque M12 nut: 27,5 Nm - 31,4 Nm

| Creator: STKU3/PDP  | Document: DB44420262EN | Dogo 2 of 4 |
|---------------------|------------------------|-------------|
| Released: IVSE1/PDP | Version: 03            | Page 3 of 4 |

## 44420262 DATA SHEET

Valid from: 14.01.2019 EPIC® POWERLOCK F6 S







Robust



Reliability



Waterproof

## Info

Connector for unscreened single-core power cables

## **Application range**

For renewable energy plants e.g. wind power For mobile and stationary power distribution For the connection of motors, transformers and generators Light & sound technology

#### **Product features**

Straight connector with M40 thread Order SKINTOP® ST-M 40 or STR-M 40 separately Contact fixing by contact retention pin, each pin can only be used once Housing without contact, order contact separately

## Remark

Photographs are not to scale and do not represent detailed images of the respective products.