

83257103	DATA SHEET	
Valid from: 17.09.2018	FLEXIMARK® Marking kit DYMO Rhino 4200	

FLEXIMARK® Marking kit DYMO Rhino 4200



General description:

- Portable marking kit with accessories for cable and component marking
- Includes DYMO Rhino Marking tape, Label printer Rhino 4200 and FLEXIMARK® Character holders
- Delivered in a solid and robust case
- Available as two different kit with tapes and holders in two sizes 9 mm and 12 mm
- Label printer DYMO Rhino 4200 with (QWERTY) keyboard layout and many more features

Product data:

Included in the FLEXIMARK® Marking kit DYMO Rhino 4200 (9 mm):

Label printer DYMO Rhino 4200	1pcs	
DYMO Rhino Marking tape Vinyl black, 9 mm		1pcs
DYMO Rhino Marking tape Vinyl white, 9 mm		1pcs
FLEXIMARK® Character holders PTE, 9,5 mm x 10 m	1pcs	
FLEXIMARK® Plier FL52ERA for character holders, 6-12 mm	1pcs	
FLEXIMARK® Plastic cable ties black, 135x2.6 mm	100pcs	

Included in the FLEXIMARK® Marking kit DYMO Rhino 4200 (12 mm):

Label printer DYMO Rhino 4200	1pcs	
DYMO Rhino Marking tape yellow, 12 mm		1pcs
DYMO Rhino Marking tape white, 12 mm		1pcs
FLEXIMARK® Character holders PTE, 12 mm x 10 m	1pcs	
FLEXIMARK® Plier FL52ERA for character holders, 6-12 mm	1pcs	
FLEXIMARK® Plastic cable ties black, 135x2.6 mm	100pcs	

Article data:

Part no.	Article designation	Tape width (mm)	Holder width (mm)	Content (unit)	PU
83257103	Marking kit Rhino 9 mm	9	9	1	1
83257104	Marking kit Rhino 12 mm	12	12	1	1

Elaborated by: FLEXIMARK: A. Lindberg	Document: DB83257103EN Version: 01	Page 1 of 3
--	---------------------------------------	-------------

83257103	DATA SHEET	
Valid from: 17.09.2018	FLEXIMARK® Marking kit DYMO Rhino 4200	

Technical data, case:

- Size: 38 x 45 x 13,5 cm
- Weight: 2,5kg

Technical data, Label printer DYMO Rhino 4200:

- Size: 17,8 x 11,7 x 5,7 cm
- Weight: 0,91kg
- Power: 6 "AA" batteries or lithium ion battery (not included)
- Keyboard layout: QWERTY
- One-touch formatting keys: Wire and cable wraps
Barcodes
Fixed-length labels
Breaker labels
Shrink tube marking
Favorite keys
Custom keys
- More features:
- Tape: Widths: 6, 9, 12 and 19 mm



Technical data, Vinyl marking tape DYMO Rhino:

- Vinyl marking tape: Strong adhesive and high resistance towards chemicals
- Colors are adapted to standards: ANSI Z535
ISO3864
ANSI A 13.1
ISO7010
ANSI606-B
- Temperature range: -18 up to +90°C



Technical data, FLEXIMARK® Character holders PTE:

- Material PTE: Polyethylene, halogen free
- Temperature range: -75°C up to +80°C
- Resistance: UV-resistant
- Approvals: UV-resistance, ageing resistance, resistance towards chemicals
(SP Tested by a third independent expert)



Delivery:

Delivered in a robust case.

Mounting:

All articles needed for mounting cable and component marking are included in the FLEXIMARK® Marking kit. FLEXIMARK® Character holders PTE are produced with FLEXIMARK® Plier FL52ERA for character holder. Cable marking is mounted together with FLEXIMARK® Plastic cable ties and DYMO Rhino Marking tapes.

Other product data:

ETIM Classification: EC001288

Elaborated by: FLEXIMARK: A. Lindberg	Document: DB83257103EN Version: 01	Page 2 of 3
--	---------------------------------------	-------------

83257103	DATA SHEET	
Valid from: 17.09.2018	FLEXIMARK® Marking kit DYMO Rhino 4200	

Advantages:

- Marking for both cables and components
- Produce your own marking directly on site
- Everything you need for marking in one robust case
- Portable label printer DYMO Rhino 4200 with many useful features
- Many different DYMO Rhino Marking tapes in assortment

Related products:

DYMO Rhino Tape materials available in FLEXIMARK® Marking assortment:

Vinyl
Polyester
Nylon
Shrink tube
Adhesive free
Wraparound vinyl

FLEXIMARK® Character holder PTE sizes in FLEXIMARK® Assortment: 6 mm
9,5 mm
12 mm
15 mm
19 mm

Foot note:

Photographs are not to scale and do not represent detailed images of the respective products.

Elaborated by: FLEXIMARK: A. Lindberg	Document: DB83257103EN Version: 01	Page 3 of 3
--	---------------------------------------	-------------