44429015	DATA SHEET	
Valid from:	EPIC [®] H-A 3 MAGD	



Description

17.09.2018

- Innovative metal and plastic housing design
- Housing in plastic or metal version. For power supply in the smallest possible space



General characteristics

Series H-A 3

Version Panel-mount base Locking mechanism single lever Protective cover yes

Protection rating, cover (DIN EN 60529)

Protection rating, mated connector (DIN EN 60529)

Protection (NEMA 250, UL50E)

IP 44 (latched)

IP 65 (latched)

4, 12 (latched)

Temperature Range -40°C to +100°C, short-term up to +125°C

Materials and surfaces

Housing, base materialZinc die-castingHousing, surfacePowder-coated, greyLeverSteel, zinc-plated

Gasket NBR

Approvals

VDE-Zulassung, VDE-REG.-Nr. B437


Standard


Safety Standard IEC 61984

44429015	DATA SHEET	MIADD
Valid from: 17.09.2018	EPIC [®] H-A 3 MAGD	WLAPP

Drawings











Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Compact, robust metal housings size H-A 3

Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB44429015EN	Daga 2 of 2
Released: IVSE1/PDP	Version: 01	Page 2 of 2