DATA SHEET 44423229 Valid from:

EPIC® MHS Bus 1x(4) CM



Description

10.05.2019

- Shielded modul for data and signal transmission
- Crimp connection for permanent vibration-proof contact
- EPIC® MH system is mateable with the market
- The mix of different functions is one plug guarantees high flexibility



General characteristics

Contact type plug Number of contacts 500 Mating cycles Material PA Inflammability class acc. with UL 94 V0 Pollution degree 3

Temperatue range -40° C to +125° C

Termination methods crimp termination: 0.14 - 2.50 mm²

Electrical characteristics

50 V Rated voltage Rated impuls voltage 0.8 kV Rated current 10 A


Standards/Approvals

Fire protection on railway vehicles according EN 45545-2

> requirement sets R22 and R23 hazard level HL1, HL2 and HL3

44423229	DATA SHEET	& LADD
Valid from: 10.05.2019	EPIC® MHS Bus 1x(4) CM	WLAPP

Drawings



Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: JOKR1/PDP	Document: DB44423229EN	Page 2 of 2
Released: IVSE1/PDP	Version: 02	