

TIE MOUNTING SOCKET TC 142**Article No.:** 61724910

Cable tie mount; for cable tie width: 7.6mm; white; Polyamide; Halogenfree;

**Details****Benefits**

- Compact construction ensures high stability
- Prism-shaped saddle of this mounting socket enables torsion-safe fastening and bundling of cables

Application

- Fastening elements for cable ties
- For fastening with screws or rivets
- Typical areas of application: Process control systems, control cabinet manufacturing and mechanical engineering

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without surcharges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive further values, such as tolerances, upon request if they are available and have been released for publication.

Technical Data

General information

Product type	Cable tie mount
Scope of delivery	without screws
Delivery Unit	500
pieces per PU	500 pc.

Electrical parameters

Product design

Total length	23.4 mm
Overall width	14.2 mm
Overall height	11 mm
Borehole diameter	5.2 mm
Material	Polyamide
Colour	white
for cable tie width	7.6 mm

Product features

Temperature min.	-40 °C
Temperature max.	85 °C
Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	No
Halogenfree	Yes
Oil-resistant	Yes

Certifications and standards

UL recognised	No
UL listed	No
cUR recognized	No

cUL listed	No
CSA certified	No
VDE certified	No
DNV-certified	No
Ecolab certified	No

Mounting socket with saddle

Article No.	Name	for cable tie width	Total length	Overall width	pieces per PU
61724510	TIE MOUNTING SOCKET TC 141	4.8 mm	17 mm	11.1 mm	500 pc.
61724910	TIE MOUNTING SOCKET TC 142	7.6 mm	23.4 mm	14.2 mm	500 pc.
61724920	TIE MOUNTING SOCKET TC 140	2.8 mm	14.2 mm	8.7 mm	500 pc.