

61820900	DATA SHEET
Valid from: 14.04.2025	Marking rings PC

Combination labelling for cables and wires, for Fast snap installation.

Material: Polycarbonate

Technical features:

Imprint	Alphanumeric and special characters
Printing	Hot stamping
Temperature range	-30°C up to +60°C
Cable cross-section	0,5 to 6mm ²
Outer Cable diameter	2,4 to 6,2mm

Additional features:

Flame retardant	V0 acc. to UL94
Halogen-free	yes
UV resistance	yes

Colour: Yellow with black print



Article no.	Designation	Imprint	Outer cable diameter mm	Cross-section mm ²
Marking rings PC 0,5 – 1,5mm²				
	Marking rings PC 10/0	0	2,4 - 3	0,5 – 1,5
61820910	Marking rings PC 10/1	1	2,4 - 3	0,5 – 1,5
61820920	Marking rings PC 10/2	2	2,4 - 3	0,5 – 1,5
61820930	Marking rings PC 10/3	3	2,4 - 3	0,5 – 1,5
61820940	Marking rings PC 10/4	4	2,4 - 3	0,5 – 1,5
61820950	Marking rings PC 10/5	5	2,4 - 3	0,5 – 1,5
61820960	Marking rings PC 10/6	6	2,4 - 3	0,5 – 1,5
61820970	Marking rings PC 10/7	7	2,4 - 3	0,5 – 1,5
61820980	Marking rings PC 10/8	8	2,4 - 3	0,5 – 1,5
61820990	Marking rings PC 10/9	9	2,4 - 3	0,5 – 1,5
61821000	Marking rings PC 10/BLANC	Blanc	2,4 - 3	0,5 – 1,5
61821010	Marking rings PC 10/A	A	2,4 - 3	0,5 – 1,5
61821020	Marking rings PC 10/B	B	2,4 - 3	0,5 – 1,5
61821030	Marking rings PC 10/C	C	2,4 - 3	0,5 – 1,5
61821040	Marking rings PC 10/D	D	2,4 - 3	0,5 – 1,5
61821050	Marking rings PC 10/E	E	2,4 - 3	0,5 – 1,5
61821060	Marking rings PC 10/F	F	2,4 - 3	0,5 – 1,5
61821070	Marking rings PC 10/G	G	2,4 - 3	0,5 – 1,5

Please refer to our current catalogue for further details.

Our laboratory will be happy to advise you on questions of resistance to aggressive media or certain oils.

Document: DB61820900EN Version: 00	Page1 from 6
---------------------------------------	--------------

61820900	DATA SHEET
Valid from: 14.04.2025	Marking rings PC

61821080	Marking rings PC 10/H	H	2,4 - 3	0,5 - 1,5
61821090	Marking rings PC 10/I	I	2,4 - 3	0,5 - 1,5
61821100	Marking rings PC 10/J	J	2,4 - 3	0,5 - 1,5
61821110	Marking rings PC 10/K	K	2,4 - 3	0,5 - 1,5
61821120	Marking rings PC 10/L	L	2,4 - 3	0,5 - 1,5
61821130	Marking rings PC 10/M	M	2,4 - 3	0,5 - 1,5
61821140	Marking rings PC 10/N	N	2,4 - 3	0,5 - 1,5
61821150	Marking rings PC 10/O	O	2,4 - 3	0,5 - 1,5
61821160	Marking rings PC 10/P	P	2,4 - 3	0,5 - 1,5
61821170	Marking rings PC 10/Q	Q	2,4 - 3	0,5 - 1,5
61821180	Marking rings PC 10/R	R	2,4 - 3	0,5 - 1,5
61821190	Marking rings PC 10/S	S	2,4 - 3	0,5 - 1,5
61821200	Marking rings PC 10/T	T	2,4 - 3	0,5 - 1,5
61821210	Marking rings PC 10/U	U	2,4 - 3	0,5 - 1,5
61821220	Marking rings PC 10/V	V	2,4 - 3	0,5 - 1,5
61821230	Marking rings PC 10/W	W	2,4 - 3	0,5 - 1,5
61821240	Marking rings PC 10/X	X	2,4 - 3	0,5 - 1,5
61821250	Marking rings PC 10/Y	Y	2,4 - 3	0,5 - 1,5
61821260	Marking rings PC 10/Z	Z	2,4 - 3	0,5 - 1,5
61821270	Marking rings PC 10//	/	2,4 - 3	0,5 - 1,5
61821280	Marking rings PC 10/. POINT	.	2,4 - 3	0,5 - 1,5
61821290	Markierhülse PC 10/, COMMA	,	2,4 - 3	0,5 - 1,5
61821300	Marking rings PC 10/:	:	2,4 - 3	0,5 - 1,5
61821310	Marking rings 10/=	=	2,4 - 3	0,5 - 1,5
61821320	Marking rings PC 10/Earth	Earth	2,4 - 3	0,5 - 1,5
61821360	Marking rings PC 10/+ PLUS	+	2,4 - 3	0,5 - 1,5
61821370	Marking rings PC 10/- MINUS	-	2,4 - 3	0,5 - 1,5
61821380	Marking rings PC 10/~ SINUS	~	2,4 - 3	0,5 - 1,5
Marking rings PC 1,5 - 2,5 mm²				
61821400	Marking rings PC 20/0	0	3 - 4	1,5 - 2,5
61821410	Marking rings PC 20/1	1	3 - 4	1,5 - 2,5
61821420	Marking rings PC 20/2	2	3 - 4	1,5 - 2,5
61821430	Marking rings PC 20/3	3	3 - 4	1,5 - 2,5
61821440	Marking rings PC 20/4	4	3 - 4	1,5 - 2,5
61821450	Marking rings PC 20/5	5	3 - 4	1,5 - 2,5
61821460	Marking rings PC 20/6	6	3 - 4	1,5 - 2,5
61821470	Marking rings PC 20/7	7	3 - 4	1,5 - 2,5

61820900	DATA SHEET
Valid from: 14.04.2025	Marking rings PC

61821480	Marking rings PC 20/8	8	3 - 4	1,5 - 2,5
61821490	Marking rings PC 20/9	9	3 - 4	1,5 - 2,5
61821500	Marking rings PC 20/ BLANC	Blanc	3 - 4	1,5 - 2,5
61821510	Marking rings PC 20/A	A	3 - 4	1,5 - 2,5
61821520	Marking rings PC 20/B	B	3 - 4	1,5 - 2,5
61821530	Marking rings PC 20/C	C	3 - 4	1,5 - 2,5
61821540	Marking rings PC 20/D	D	3 - 4	1,5 - 2,5
61821550	Marking rings PC 20/E	E	3 - 4	1,5 - 2,5
61821560	Marking rings PC 20/F	F	3 - 4	1,5 - 2,5
61821570	Marking rings PC 20/G	G	3 - 4	1,5 - 2,5
61821580	Marking rings PC 20/H	H	3 - 4	1,5 - 2,5
61821590	Marking rings PC 20/I	I	3 - 4	1,5 - 2,5
61821600	Marking rings PC 20/J	J	3 - 4	1,5 - 2,5
61821610	Marking rings PC 20/K	K	3 - 4	1,5 - 2,5
61821620	Marking rings PC 20/L	L	3 - 4	1,5 - 2,5
61821630	Marking rings PC 20/M	M	3 - 4	1,5 - 2,5
61821640	Marking rings PC 20/N	N	3 - 4	1,5 - 2,5
61821650	Marking rings PC 20/O	O	3 - 4	1,5 - 2,5
61821660	Marking rings PC 20/P	P	3 - 4	1,5 - 2,5
61821670	Marking rings PC 20/Q	Q	3 - 4	1,5 - 2,5
61821680	Marking rings PC 20/R	R	3 - 4	1,5 - 2,5
61821690	Marking rings PC 20/S	S	3 - 4	1,5 - 2,5
61821700	Marking rings PC 20/T	T	3 - 4	1,5 - 2,5
61821710	Marking rings PC 20/U	U	3 - 4	1,5 - 2,5
61821720	Marking rings PC 20/V	V	3 - 4	1,5 - 2,5
61821730	Marking rings PC 20/W	W	3 - 4	1,5 - 2,5
61821740	Marking rings PC 20/X	X	3 - 4	1,5 - 2,5
61821750	Marking rings PC 20/Y	Y	3 - 4	1,5 - 2,5
61821760	Marking rings PC 20/Z	Z	3 - 4	1,5 - 2,5
61821770	Marking rings PC 20//	/	3 - 4	1,5 - 2,5
61821780	Marking rings PC 20/. POINT	.	3 - 4	1,5 - 2,5
61821790	Marking rings PC 20/, COMMA	,	3 - 4	1,5 - 2,5
61821800	Marking rings PC 20/:	:	3 - 4	1,5 - 2,5
61821810	Marking rings PC 20/=	=	3 - 4	1,5 - 2,5
61821820	Marking rings PC 20/ Erarth	Earth	3 - 4	1,5 - 2,5
61821860	Marking rings PC 20/+ PLUS	+	3 - 4	1,5 - 2,5
61821870	Marking rings PC 20/- MINUS	-	3 - 4	1,5 - 2,5

61820900	DATA SHEET
Valid from: 14.04.2025	Marking rings PC

61821880	Marking rings PC 20/~ SINUS	~	3 - 4	1,5 - 2,5
Marking rings PC 2,5 - 4mm²				
61821900	Marking rings PC 30/0	0	4 - 5	2,5 - 4
61821910	Marking rings PC 30/1	1	4 - 5	2,5 - 4
61821920	Marking rings PC 30/2	2	4 - 5	2,5 - 4
61821930	Marking rings PC 30/3	3	4 - 5	2,5 - 4
61821940	Marking rings PC 30/4	4	4 - 5	2,5 - 4
61821950	Marking rings PC 30/5	5	4 - 5	2,5 - 4
61821960	Marking rings PC 30/6	6	4 - 5	2,5 - 4
61821970	Marking rings PC 30/7	7	4 - 5	2,5 - 4
61821980	Marking rings PC 30/8	8	4 - 5	2,5 - 4
61821990	Marking rings PC 30/9	9	4 - 5	2,5 - 4
61822000	Marking rings PC 30/ BLANC	Blanc	4 - 5	2,5 - 4
61822010	Marking rings PC 30/A	A	4 - 5	2,5 - 4
61822020	Marking rings PC 30/B	B	4 - 5	2,5 - 4
61822030	Marking rings PC 30/C	C	4 - 5	2,5 - 4
61822040	Marking rings PC 30/D	D	4 - 5	2,5 - 4
61822050	Marking rings PC 30/E	E	4 - 5	2,5 - 4
61822060	Marking rings PC 30/F	F	4 - 5	2,5 - 4
61822070	Marking rings PC 30/G	G	4 - 5	2,5 - 4
61822080	Marking rings PC 30/H	H	4 - 5	2,5 - 4
61822090	Marking rings PC 30/I	I	4 - 5	2,5 - 4
61822100	Marking rings PC 30/J	J	4 - 5	2,5 - 4
61822110	Marking rings PC 30/K	K	4 - 5	2,5 - 4
61822120	Marking rings PC 30/L	L	4 - 5	2,5 - 4
61822130	Marking rings PC 30/M	M	4 - 5	2,5 - 4
61822140	Marking rings PC 30/N	N	4 - 5	2,5 - 4
61822150	Marking rings PC 30/O	O	4 - 5	2,5 - 4
61822160	Marking rings PC 30/P	P	4 - 5	2,5 - 4
61822170	Marking rings PC 30/Q	Q	4 - 5	2,5 - 4
61822180	Marking rings PC 30/R	R	4 - 5	2,5 - 4
61822190	Marking rings PC 30/S	S	4 - 5	2,5 - 4
61822200	Marking rings PC 30/T	T	4 - 5	2,5 - 4
61822210	Marking rings PC 30/U	U	4 - 5	2,5 - 4
61822220	Marking rings PC 30/V	V	4 - 5	2,5 - 4
61822230	Marking rings PC 30/W	W	4 - 5	2,5 - 4
61822240	Marking rings PC 30/X	X	4 - 5	2,5 - 4
61822250	Marking rings PC 30/Y	Y	4 - 5	2,5 - 4

61820900	DATA SHEET
Valid from: 14.04.2025	Marking rings PC

61822260	Marking rings PC 30/Z	Z	4 - 5	2,5 - 4
61822270	Marking rings PC 30//	/	4 - 5	2,5 - 4
61822280	Marking rings PC 30/. POINT	.	4 - 5	2,5 - 4
61822290	Marking rings PC 30/, COMMA	,	4 - 5	2,5 - 4
61822300	Marking rings PC 30/:	:	4 - 5	2,5 - 4
61822310	Marking rings PC 30/=	=	4 - 5	2,5 - 4
61822320	Marking rings PC 30/ Earth	Earth	4 - 5	2,5 - 4
61822360	Marking rings e PC 30/+ PLUS	+	4 - 5	2,5 - 4
61822370	Marking rings PC 30/- MINUS	-	4 - 5	2,5 - 4
61822380	Marking rings PC 30/~ SINUS	~	4 - 5	2,5 - 4
Marking rings PC 4 – 6 mm²				
61822400	Marking rings PC 40/0	0	5 – 6,2	4 - 6
61822410	Marking rings PC 40/1	1	5 – 6,2	4 - 6
61822420	Marking rings PC 40/2	2	5 – 6,2	4 - 6
61822430	Marking rings PC 40/3	3	5 – 6,2	4 - 6
61822440	Marking rings PC 40/4	4	5 – 6,2	4 - 6
61822450	Marking rings PC 40/5	5	5 – 6,2	4 - 6
61822460	Marking rings PC 40/6	6	5 – 6,2	4 - 6
61822470	Marking rings PC 40/7	7	5 – 6,2	4 - 6
61822480	Marking rings PC 40/8	8	5 – 6,2	4 - 6
61822490	Marking rings PC 40/9	9	5 – 6,2	4 - 6
61822500	Marking rings PC 40/ BLANC	Blanc	5 – 6,2	4 - 6
61822510	Marking rings PC 40/A	A	5 – 6,2	4 - 6
61822520	Marking rings PC 40/B	B	5 – 6,2	4 - 6
61822530	Marking rings PC 40/C	C	5 – 6,2	4 - 6
61822540	Marking rings PC 40/D	D	5 – 6,2	4 - 6
61822550	Marking rings PC 40/E	E	5 – 6,2	4 - 6
61822560	Marking rings PC 40/F	F	5 – 6,2	4 - 6
61822570	Marking rings PC 40/G	G	5 – 6,2	4 - 6
61822580	Marking rings PC 40/H	H	5 – 6,2	4 - 6
61822590	Marking rings PC 40/I	I	5 – 6,2	4 - 6
61822600	Marking rings PC 40/J	J	5 – 6,2	4 - 6
61822610	Marking rings PC 40/K	K	5 – 6,2	4 - 6
61822620	Marking rings PC 40/L	L	5 – 6,2	4 - 6
61822630	Marking rings PC 40/M	M	5 – 6,2	4 - 6
61822640	Marking rings PC 40/N	N	5 – 6,2	4 - 6

61820900	DATA SHEET
Valid from: 14.04.2025	Marking rings PC

61822650	Marking rings PC 40/O	O	5 – 6,2	4 – 6
61822660	Marking rings PC 40/P	P	5 – 6,2	4 – 6
61822670	Marking rings PC 40/Q	Q	5 – 6,2	4 – 6
61822680	Marking rings PC 40/R	R	5 – 6,2	4 – 6
61822690	Marking rings PC 40/S	S	5 – 6,2	4 – 6
61822700	Marking rings PC 40/T	T	5 – 6,2	4 – 6
61822710	Marking rings PC 40/U	U	5 – 6,2	4 – 6
61822720	Marking rings PC 40/V	V	5 – 6,2	4 – 6
61822730	Marking rings PC 40/W	W	5 – 6,2	4 – 6
61822740	Marking rings PC 40/X	X	5 – 6,2	4 – 6
61822750	Marking rings PC 40/Y	Y	5 – 6,2	4 – 6
61822760	Marking rings PC 40/Z	Z	5 – 6,2	4 – 6
61822770	Marking rings PC 40//	/	5 – 6,2	4 – 6
61822780	Marking rings PC 40/. POINT	.	5 – 6,2	4 – 6
61822790	Marking rings PC 40/, COMMA	,	5 – 6,2	4 – 6
61822800	Marking rings PC 40/:	:	5 – 6,2	4 – 6
61822810	Marking rings PC 40/=	=	5 – 6,2	4 – 6
61822820	Marking rings PC 40/ Earth	Earth	5 – 6,2	4 – 6
61822860	Marking rings PC 40/+ PLUS	+	5 – 6,2	4 – 6
61822870	Marking rings PC 40/- MINUS	-	5 – 6,2	4 – 6
61822880	Marking rings PC 40/~ SINUS	~	5 – 6,2	4 – 6

Commodity product, not a Lapp product.