

ASSORTMENT BOX DIN II**Article No.:** 61802041

End sleeve; suitable crimp-insert: PEW 12.090; transparent; Electrolytic copper Tin-plated

**Details****Benefits**

- Convenient assortment boxes - several diameters always at your fingertips

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without surcharges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive further values, such as tolerances, upon request if they are available and have been released for publication.

Technical Data**General information**

Product type	End sleeve
Packaging type	Assortment box

Delivery Unit	1
suitable crimp-insert	PEW 12.090

Electrical parameters**Product design**

For cross-section (min.)	0.5 mm ²
For cross-section (max.)	2.5 mm ²
Material connector	Electrolytic copper
material isolation	Polypropylene
Surface protection	Tin-plated
Colour	transparent
cable lug design	End sleeve

Product features

Temperature min.	-5 °C
Temperature max.	105 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
Corrosion-resistant	Yes
Halogenfree	No
Oil-resistant	Yes

Certifications and standards

CE marked	No
UKCA marked	No
EAC certified	Not required
EAC certification number	Отказное письмо № 39
UL recognised	No
UL listed	No

cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No

assorted boxes end sleeves

Article No.	Name	suitable crimp-insert	For cross-section (min.)	For cross-section (max.)	Delivery Unit
61794720	ASSORTMENT BOX AHI I	PEW 12.090	0.25 mm ²	1 mm ²	1
61794730	ASSORTMENT BOX AHI II	PEW 12.090	0.5 mm ²	2.5 mm ²	1
61794740	ASSORTMENT BOX AHI III	PEW 12.090,PEW 12.091	4 mm ²	16 mm ²	1
61802040	ASSORTMENT BOX DIN I	PEW 12.090	0.25 mm ²	1 mm ²	1
61802041	ASSORTMENT BOX DIN II	PEW 12.090	0.5 mm ²	2.5 mm ²	1
61802042	ASSORTMENT BOX DIN III	PEW 12.090,PEW 12.091	4 mm ²	16 mm ²	1
61802046	ASSORTMENT BOX TWIN	PEW 12.090-6	0.75 mm ²	2.5 mm ²	1