

7433501361	DATA SHEET	
Valid from: 19.02.2026	EPIC® MC04C2LSAPNB22RK50	

Description

- Sensor/actuator TPU-cable, unshielded, with LED Display
- M12 Connector, A-coding, 4 Pin



Product variations

Article no.	Article description	P1 - cable end	Length (mm)
7433501361	EPIC® MC04C2LSAPNB22RK50	coupling, straight	5000 +100/-20

Other lengths are available on request.

Connector, general characteristics

Coding	A-Coding
Number of poles / pins	4
Product standard	IEC 61076-2-101 (2024)
Shielded	No
Protection class	IP 67
Pollution degree	3
Ambient temperature (connected)	-25 up to +80°C (Flexible) -40 up to +80°C (Fixed)
Plugging cycles	≥ 100
Tightening torque	Recommended:0.4 Nm Max:0.8 Nm

Connector, electrical properties

Rated voltage	12V
Rated surge voltage	N/A
Rated current	4 A
Insulation resistance	≥ 100 MΩ
Contact resistance of connector	≤ 5 mΩ

Connector, materials

Contacts	Phosphor, gold plated
Insert	PA66+GF
Overmold	TPU/ NC
Threaded part	Brass, nickel plated
Sealing	FKM

7433501361	DATA SHEET	
Valid from: 19.02.2026	EPIC® MC04C2LSAPNB22RK50	

Cable, general characteristics

AWM style	UL20549
Conductor cross-section	22 AWG (0.34mm ²)
Number of conductors	3 (1. Brown, 2. White, 4. Blue, 4. Black)
Core outer diameter	1.2 ±0.1mm
Jacket outer diameter	4.5±0.2mm
Cable weight	26.7 ± 3 kg/km
Temperature rating	-40 up to +80°C
Flammability test	H; CSAFT2
Halogen-free	No
Oil resistance	No

Cable, electrical properties


Rated voltage	300 V
Conductor resistance	MAX 59.4 Ω/km at 20°C
Dielectric strength	2000V / min.

Cable, materials


Conductor	Tinned copper
Conductor insulation	HD-PE
Jacket	TPU, Black

7433501361	DATA SHEET	
Valid from: 19.02.2026	EPIC® MC04C2LSAPNB22RK50	

Drawings



Cross section



Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: Drake Long / PDCF Released: SOLI1/ PDCF	Document: DB7433501343EN Version: 00	Page 3 of 3
---	---	-------------