


45612000	<b>DATA SHEET</b>	
valid from: 27.10.2025	<b>COPPER ROPE BARE CLASS 2</b>	

### Application

COPPER ROPE BARE CLASS 2 are suitable for earthing devices and potential equalisation on machine parts and EDP systems and also for the construction of meshed equipotential bonding systems.

### Design

Conductor multi-wire bare copper conductor acc. IEC 60228 resp. EN IEC 60228, class 2  
Insulation no insulation

**Environmental information** These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

**Note** Trade product, no Lapp product

**Table 1**  
**Dimensional and electrical characteristics**

Nominal cross section *	Outer diameter	Tolerance	Maximum resistance of conductor at 20°C (bare wire) acc. to IEC 60228 resp. EN IEC 60228
(mm <sup>2</sup> )	(mm)	(mm)	(Ω/km)
6	3.18	+/- 0.3	3.08
10	4.14	+/- 0.3	1.83
16	5.10	+/- 0.4	1.15
25	6.30	+/- 0.4	0.727
35	7.50	+/- 0.4	0.524
50	8.70	+/- 0.5	0.387
70	10.50	+/- 0.5	0.268
95	12.50	+/- 0.5	0.193

\* Cross section is reference value (for information only)

Creator: LABU / PDC	Document: DB45612000EN	Page 1 of 1
Released: ALTE / PDC	Version: 01	