

22260371	DATA SHEET	
Valid from: 21.12.2023	AB-C4-M8MS-(L*)PUR-M12FS	

Product description

- Sensor/actuator cable, 4-pol, PUR halogen-free, black
- Straight M8-plug on straight M12-jack



General characteristics

Number of pins	4
Ambient temperature	-25 °C to +90 °C (-13°F to 194°F) (plug / jack) -40 °C to +80 °C (-40°F to 176°F) (cable, fixed installation) -25 °C to +80 °C (-13°F to 176°F) (cable, movable installation)
Degree of protection	IP65 / IP67 / IP68
Coding	A-standard
Tightening torque	0,4 Nm (M12-connector) 0,2 Nm (M8-connector)
Plugging cycles	≥ 100

Variation

Article number	Description	Length [m]	Configuration
22262163	AB-C4-M8MS-0,5PUR-M12FS	0,5	straight – straight
22262164	AB-C4-M8MS-1,0PUR-M12FS	1	straight – straight
22260371	AB-C4-M8MS-1,5PUR-M12FS	1,5	straight – straight
22262165	AB-C4-M8MS-2,0PUR-M12FS	2	straight – straight
22260373	AB-C4-M8MS-2,5PUR-M12FS	2,5	straight – straight
22262166	AB-C4-M8MS-3,0PUR-M12FS	3	straight – straight
22260372	AB-C4-M8MS-15,0PUR-M12FS	15	straight – straight

Additional note

Data sheet also valid for variant lengths. Other lengths on request.

Electrical properties

Rated voltage	48 V AC / 60 V DC
Rated current	4 A
Overvoltage category	II
Pollution degree	3

Mechanical properties

Plug, jack

Inflammability class in accordance with UL 94	HB
Contact, material	CuSn
Contact carrier, material	TPU GF
Contact surface, material	Ni/Au
Knurl, material	Zinc diecasting, nickel-plated
Handle, material	TPU, flame retardant, self-extinguishing
Sealing, material	NBR

Creator: THLE3/PDP Released: IVSE1/PDP	Document: DB22260371EN Version: 00	Page 1 of 3
---	---------------------------------------	-------------

22260371	DATA SHEET	
Valid from: 21.12.2023	AB-C4-M8MS-(L*)PUR-M12FS	

Line

Cable construction	4 x AWG24/32
Signal line, construction	32 x 0,1 mm
Conductor cross-section	0,25 mm ²
Conductor diameter including isolation	1,17 mm ± 0,02 mm
Cable outer diameter	4,4 mm ± 0,15mm
Insulation color	brown, white, blue, black
Sheath color	grey-black, RAL 7021
Number of bending cycles	10.000.000
Bending radius	44 mm
Traveling distance	10 m
Traveling speed	3 m/s
Acceleration	5 m/s ²
Cable weight	23 kg/km
Outer coating, material	PUR
Wire insulation, material	PP
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Conductor resistance	≤ 78 Ω/km (at 20 °C)
Flame resistance	acc. to UL 758 / 1581 FT2 DIN EN 60332-2-2 (20 s)
Halogen-free	acc. to DIN VDE 0472 Part 815
Oil resistance	acc. to DIN EN 60811-2-1
Other resistances	resistant to hydrolysis and microbes good resistant to acids, lyes and solvents limited UV resistance acc. to DIN EN ISO 4892-2-A suitable for drag chains, silicone-free







Standards

Product standard, M12 connector	IEC 61076-2-101
Product standard, M8 connector	IEC 61076-2-104
UL-Listed, E-File	E249137

Creator: THLE3/PDP Released: IVSE1/PDP	Document: DB22260371EN Version: 00	Page 2 of 3
---	---------------------------------------	-------------

22260371	DATA SHEET	
Valid from: 21.12.2023	AB-C4-M8MS-(L*)PUR-M12FS	

Technical drawing



Application range
 For increased mechanical load and rough operating conditions

Note
 Photographs are not true to scale and do not represent detailed images of the respective products.