### 75009691

## **DATA SHEET**

Valid from: 18.09.2020

**EPIC® POWER LS1 KIT A1 5+PE** 



## Description

- Circular connectors for servomotors and power supply
- High power at smallest installation space
- Optimal solution for electric motors
- EMC-optimised design
- · Safety use in field environment by high protection class



### **General Characteristics**

Series POWER LS 1

Version Front wall mounting for male contacts

Pin configuration 5+PE
Rated voltage (V) 630 V
Rated impulse voltage 6 kV
Rated current (A) 25 A
Contact resistance <4 mOhm

Contacts included Yes

Contacts Gold plated brass

Number of contacts 5+PE

Termination methods Crimp termination: 0.5 - 2.5 mm² (2 mm contacts)

Cable clamping range Ø 2,7 mm (4x)

Protection IP 68
Cycle of mechanical operation 500

Temperature range -25°C to +125°C

Degree of soiling 3

### **Materials and Surfaces**

Housing Nickel-plated zinc die-casting, nickel-plated brass

Insert PA Seal FPM

### **Approvals**

VDE-Approval, VDE-REG.-Nr. B025 UL-File-Number E249137

### **Standard**

Safety Standard IEC 61984, UL2238; CSA 22.2 182.3



Creator: STKU3/PDP Document: DB75009691EN
Released: IVSE1/PDP Version: 01
Page 1 of 3


# 75009691 DATA SHEET

Valid from: 18.09.2020

## **EPIC® POWER LS1 KIT A1 5+PE**



## **Technical Drawings**





Good chemical resistance



Corrosion-resistant



Industrial machinery and plant engineering



Maximum vibration protection



Mechanical resistance



Assembly time



Space requirement



Robust

Creator: STKU3/PDP	Document: DB75009691EN	Page 2 of 3
Released: IVSE1/PDP	Version: 01	

# 75009691 DATA SHEET

Valid from: 18.09.2020

## **EPIC® POWER LS1 KIT A1 5+PE**





Waterproof



Wind Energy



Variety of approval certifications

## **Application range**

Plant engineering Servo drives and servo assemblies

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.