LAPP Korea

DATA SHEET



ÖLFLEX® TRAIN 4GKW

LK 12111604RD

Version: 04 Date: 22.03.2019

Designation 1.

ÖLFLEX® TRAIN 4GKW

2. **Application**

For protected installations inside and outside of rail vehicles and buses and other rail vehicles used for the connection of fixed and moved parts. Suitable for the wiring of switchboards, converters and distribution boxes. Due to the doubleinsulated design, these cables can be classified as short circuit and earth fault-proof. The thin outer layer protects against the effects of mineral oil fuels and ozone.

3. ▶ Design <</p>

- Conductor: Fine wire strands of non-porous tinned copper wires according IEC 60228, Class 5
- Conductor resistance according VDE 0295, Class 5
- Separator tape (if necessary)
- Core insulation: electron beam cross-linked polymer compound, halogen free and flame retardant The insulation colour is natural.
- Core sheath: electron beam cross-linked polymer compound, halogen free and flame retardant The sheath colour is black.

►Technical data <

1.8/3kV AC Nominal voltage U₀/U (AC) Nominal voltage V₀ (DC) 2.7kV DC

6.5 kV Test voltage

Temperature range fixed installed:

-40 °C up to +125 °C max.

occasional flexing

-35 °C up to +90 °C max.

Short circuit temperature +200 °C

Minimum bending radius (≤12mm) fixed installation: 3 x cable diameter

> 4 x cable diameter occasional flexing: 4 x cable diameter fixed installation:

(>12mm) occasional flexing: 5 x cable diameter

5. Fire performance

BS6853 Interior use la,lb,ll

Exterior use la,lb,ll

Vertical flame spread of bunched wires and cables BS 6853

Smoke density BS 6853 appendix D Toxicity of gases BS 6853 appendix B R < 1.0

Document: LK12111604RD Originator: Y.W.Ahn / PD Supersedes version: 03 from 08.09.2017 Approved: Terry S H Ko / PD

page 1 of 3

LAPP Korea

DATA SHEET



ÖLFLEX® TRAIN 4GKW

LK 12111604RD

Version: 04 Date: 22.03.2019

EN 45545-2 hazard level HL 1, HL 2, HL 3

Vertical flame propagation for a single insulated wire or cable

Vertical flame spread of bunched wires and cables

Smoke density

Toxicity of gases

EN 60332-1-2

EN 50305

EN 61034-2

EN 50305

NFPA 130

Vertical flame spread of bunched wires and cables FT4/IEEE1202
Smoke density ANSI/UL1685
Toxicity of gases BSS-7239

6. Cable make up

6.1 Conductor

- Conductor make up: Fine wire strands of tinned copper according to IEC 60228/EN 60228 resp. VDE 0295 class 5
- Conductor resistance acc. to EN 60228 resp. VDE 0295 class 5 for tinned copper wires
- Separator tape (if necessary)

6.2 Inner insulation

- Material: temperature resistant electron beam cross-linked polymer, halogen free and highly flame retardant Manufacturer and compound designation:
- Colours : natural

6.3 Outer insulation

- Material: temperature resistant electron beam cross-linked polymer, halogen free and highly flame retardant Manufacturer and compound designation:
- Colours : black

Originator: Y.W.Ahn / PD Approved: Terry S H Ko / PD Document: LK12111604RD

Supersedes version: 03

from 08.09.2017

page 2 of 3

LAPP Korea

DATA SHEET



ÖLFLEX® TRAIN 4GKW

LK 12111604RD

Version: 04 Date: 22.03.2019

6.4 ▶ Dimension ◀

| Conductor | Inner Insulation | Outer Insulation | Outer diameter |
|---------------|---------------------|---------------------|----------------|
| Cross section | Thickness | Thickness | Approx. |
| (mm²) | (mm) | (mm) | (mm) |
| 1.5 | 0.6 | 0.4 | 3.6 |
| 2.5 | 0.6 | 0.4 | 4.0 |
| 4 | 0.6 | 0.4 | 4.5 |
| 6 | 0.7 | 0.4 | 5.3 |
| 10 | 0.8 | 0.4 | 6.5 |
| 16 | 0.8 | 0.6 | 8.6 |
| 25 | 0.9 | 0.7 | 10.3 |
| 35 | 1.0 | 0.7 | 11.9 |
| 50 | 1.0 | 0.8 | 14.3 |
| 70 | 1.0 | 0.8 | 16.2 |
| 95 | 1.0 | 0.8 | 18.1 |
| 120 | 1.2 | 0.9 | 20.4 |
| 150 | 1.2 | 0.9 | 22.2 |
| 185 | 1.2 | 1.1 | 24.6 |
| 240 | 1.2 | 1.1 | 27.5 |
| 300 | 1.3 | 1.2 | 30.6 |
| 400 | 1.3 | 1.3 | 34.3 |

7. Common requirements

RoHS: Dangerous and forbidden substances according to EC-Directive 2011/65/EU regarding Restriction of

the use of certain hazardous substances (RoHS), are not allowed during manufacturing.

REACH: All materials used in the manufacturing process of the product are subject to the EC-Regulation

No.1907/2006 regarding Registration, Evaluation, Authorization and Restriction of Chemicals

(REACH).

If substances based on the current Candidate List are used, they shall be listed with their designation

and their concentration.