

CE6326	DATA SHEET	
Valid from: 14.11.2018	EPIC® CE6326 RJ45 Connector for MCS 8 RJ45	

Description

- The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.
- RJ45 connector for use in the module MCS 8 RJ45



General Characteristics

Series	MC Module
Version	Male
Number of Contacts	8
Termination Methods	IDC/piercing termination: Cat 5, AWG 24-26
Temperature Range	-20°C to +85°C

Mechanical Characteristics

Cycle of mechanical operation	100
-------------------------------	-----

Electrical Characteristics

Rated Voltage	max. 125V
Rated Current	max. 1.5 A
Degree of Soiling	3

Materials and Surfaces

Contact	Copper alloy, gold-plated
---------	---------------------------



Automation



Industrial machinery and plant engineering



Wind Energy

Application range

Plant engineering
Control engineering

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DBCE6326EN Version: 01	Page 1 of 1
---	-------------------------------------	-------------