

Valid from: 17.09.2018

EPIC[®] H-A 16 AD-LB



Description

- These connectors are attractive because of their compact housing.
- Small and compact for applications with high number of contacts



General characteristics

Series Version Locking Protection cover Protection (DIN EN 60529) Protection (NEMA 250, UL50E) Temperature range	H-A 16 Panel-mount base single lever yes IP 65 (latched) 4, 12 (latched) -40°C to +100°C, short-term up to +125°C
Materials and surfaces	
Housing Protection cover Lever Gasket	Aluminium alloy, powder-coated, grey Zinc alloy, powder-coated, grey Steel, zinc-plated NBR
Approvals	
VDE-Approval, VDE-REGNr.	B437
Standards	
Safety Standard	IEC 61984

	Creator: MANA2/PDP	Document: DB70474000EN	Dega 1 of 2		
	Released: IVSE1/PDP	Version: 01	Page 1 of 2		
We reserve all rights according to DIN ISO 16016					


Valid from:



EPIC[®] H-A 16 AD-LB

17.09.2018 Drawings









Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info Compact, robust metal housings size H-A 16

Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB70474000EN	Dage 2 of 2		
Released: IVSE1/PDP	Version: 01	Page 2 of 2		
We reserve all rights according to DIN ISO 16016.				