

## ÖLFLEX® TRAIN 4GKW

HDB85 165001EN

Version: 09

Date: 26.Mar.2026

### 1. Designation

ÖLFLEX® TRAIN 4GKW

### 2. Application

For protected installations inside and outside of rail vehicles and buses and other rail vehicles used for the connection of fixed and moved parts. Suitable for the wiring of switchboards, converters and distribution boxes. Due to the double-insulated design, these cables can be classified as short circuit and earth fault-proof. The thin outer layer protects against the effects of mineral oil fuels and ozone.

### 3. Design

- Norm references: EN 50264-3-1, type OM
- Conductor: Fine wire strands of non-porous tinned copper wires according to IEC 60228, Class 5  
Conductor resistance according to VDE 0295, Class 5  
Separator tape (if necessary)
- Inner insulation: Electron beam cross-linked polymer compound, halogen free and flame retardant  
The insulation colour: White
- Outer insulation: Electron beam cross-linked polymer compound, halogen free and flame retardant,  
UV resistance  
The sheath colour: Black

### 4. Technical data

Nominal voltage $U_0/U$ ( $U_m$ )	1.8/3 (3.6) kV AC
Nominal voltage $V_0/V$	2.7/5.4 kV DC
Test voltage	6.5 kV
Temperature range	Fixed installed: -40 °C up to +125 °C max.
	Occasional flexing: -35 °C up to +90 °C max.
Short circuit temperature	+200 °C
Minimum bending radius ( $\leq 12\text{mm}$ )	Fixed installation: 3 x cable diameter Occasional flexing: 4 x cable diameter
( $> 12\text{mm}$ )	Fixed installation: 4 x cable diameter Occasional flexing: 5 x cable diameter
UV resistance	Acc. to EN 50525-1 are cables with black sheath suitable for a permanent outdoor use.

### 5. Fire performance

<b>BS6853</b>	Interior use	la,lb,II
	Exterior use	la,lb,II
Vertical flame spread of bunched wires and cables		BS 6853
Smoke density		BS 6853 appendix D
Toxicity of gases		BS 6853 appendix B R < 1.0

**ÖLFLEX® TRAIN 4GKW**
**HDB85 165001EN**
**Version: 09**
**Date: 26.Mar.2026**
**EN 45545-2**

hazard level

HL 1, HL 2, HL 3

 Vertical flame propagation for a single insulated wire or cable  
 Vertical flame spread of bunched wires and cables  
 Smoke density  
 Toxicity of gases

 EN 60332-1-2  
 EN 50305  
 EN 61034-2  
 EN 50305

**NFPA 130**

 Vertical flame spread of bunched wires and cables  
 Smoke density  
 Toxicity of gases

 FT4/IEEE1202  
 ANSI/UL1685  
 BSS-7239

## 6. Cable make up

### 6.1 Conductor

- Conductor make up: Fine wire strands of tinned copper according to IEC 60228/EN 60228 resp. VDE 0295 class 5
- Conductor resistance acc. to EN 60228 resp. VDE 0295 class 5 for tinned copper wires
- Separator tape (if necessary)

### 6.2 Inner insulation

- Material: Temperature resistant electron beam cross-linked polymer, halogen free and highly flame retardant  
Manufacturer and compound designation:
- Colours: White

### 6.3 Outer insulation

- Material: Temperature resistant electron beam cross-linked polymer, halogen free and highly flame retardant  
Manufacturer and compound designation:
- Colours: Black

### 6.4 Dimension

Part no.	Conductor	Inner Insulation	Outer Insulation	Outer diameter
	Cross section (mm <sup>2</sup> )	Thickness (mm)	Thickness (mm)	Approx. (mm)
85165001	1.5	0.6	0.4	3.6
85165002	2.5	0.6	0.4	4.0
85165003	4	0.6	0.4	4.5
85165004	6	0.7	0.4	5.3
85165005	10	0.8	0.4	6.5
85165006	16	0.8	0.6	8.6

**ÖLFLEX® TRAIN 4GKW**
**HDB85165001EN**
**Version: 09**
**Date: 26.Mar.2026**

Part no.	Conductor	Inner Insulation	Outer Insulation	Outer diameter
	Cross section (mm <sup>2</sup> )	Thickness (mm)	Thickness (mm)	Approx. (mm)
85165007	25	0.9	0.7	10.3
85165008	35	1.0	0.7	11.9
85165009	50	1.0	0.8	14.3
85165010	70	1.0	0.8	16.2
85165011	95	1.0	0.8	18.1
85165012	120	1.2	0.9	20.4
85165013	150	1.2	0.9	22.2
85165014	185	1.2	1.1	24.6
85165015	240	1.2	1.1	27.5
85165016	300	1.3	1.2	30.6
85165017	400	1.3	1.3	34.3

## 7. Common requirements

**RoHS:** Dangerous and forbidden substances according to EC-Directive 2011/65/EU regarding Restriction of the use of certain hazardous substances (RoHS), are not allowed during manufacturing.

**REACH:** All materials used in the manufacturing process of the product are subject to the EC-Regulation No.1907/2006 regarding Registration, Evaluation, Authorization and Restriction of Chemicals (**REACH**).

If substances based on the current Candidate List are used, they shall be listed with their designation and their concentration.