# 22260118

# **DATA SHEET**

Valid from: 17.09.2018

AB-C4-DSI-M12FS-PG9-0,5



#### Description

- Sensor/Actuator flush-type socket, 4-pos., M12 with rapid interlock
- Rear/screw mounting with PG9 thread, with 0.5 m TPE litz wire, 4 x 0.34 mm<sup>2</sup>



#### General characteristics

Number of poles 4

Connection type Fixed connection

Status indicator No

Coding A-standard

Degree of protection IP 67

Inflammability class acc. to UL 94 V0

Ambient temperature (operation) -25 to +90 °C (-13 to 194 °F) (cable, fixed installation)

-25 to +85 °C (-13 to 185 °F) (connector)

#### **Electrical properties**

 $\begin{array}{ll} \mbox{Insulation resistance} & \mbox{20 m} \Omega^* km \\ \mbox{Contact resistance} & \mbox{3 m} \Omega \end{array}$ 

#### **Mechanical properties**

#### Connector

Contact, material CuZn
Contact surface, material Au
Contact carrier, material PA 66

Knurl, material Zinc die-cast (nickel-plated)

Sealing, material NBR

#### Line

Cable type TPE litz wire

Conductor, material Tin plated copper litz wires

Core insulation, material PE
Conductor diameter including insulation 1.2 mm
Conductor cross section 0.34 mm²
AWG signal line 22

Creator: MOKO2/PDP	Document: DB22260118EN	Page 1 of 2
Released: IVSE1/PDP	Version: 03	

# 22260118


# **DATA SHEET**


Valid from: 17.09.2018


AB-C4-DSI-M12FS-PG9-0,5





# **Technical drawing**











# **Application range**

Connection of enclosures and cabinets

#### Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: MOKO2/PDP	Document: DB22260118EN	Page 2 of 2
Released: IVSE1/PDP	Version: 03	