0162006 DATA SHEET

Valid from: 01.04.2019

IEC compensating cable KN 4 L-S 2x1,5 oval



Application

The compensating cable KN 4 L-S 2 x 1,5 mm² is a glass fibre insulated cable which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for fixed installation in dry rooms and may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range. The steel wire armouring serves as mechanical protection.

Design

Conductor 1.5 mm² (48 x 0.20 mm)

Conductor material KCA alloying, accuracy class 2 according IEC 60584

Positive conductor: Fe (iron)

Negative conductor: CuNi (cupronickel)

Core insulation Glass fibre covering

Core identification Positive conductor: green marked

Negative conductor: white marked

Core layering Cores parallel next to each other

Outer sheath Glass fibre braiding with interweaved, green identification thread

Armouring Galvanized steel wire braiding with interweaved, green identification thread

Electrical properties

Limiting deviation class 2 ±100 µV (±2.5 °C) / measuring point temperature +900 °C

Mechanical and thermal properties

Temperature range occasional flexing: -25 °C up to +200 °C

Minimum bending radius occasional flexing: 15 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2