

381167293	DATA SHEET	
Valid from: 10.07.2025	EPIC® H-K 006/6 MAS	

Description

- 6 + 6 Pin inserts for harnessing
- Suitable for the general machineryand plant engineering, renewable energy and plastic industry
- 6 power contacts
6 Signal contacts



Images may vary

General Characteristics

Series	H-K 6/6
Version	Male
Design Size	24B
Number of Contacts	12 + PE
Number of Power Contacts	6
Number of Signal Contacts	6
Termination Method	Axial screw termination / Screw termination
Power Conductor Cross-Section	16 – 35 mm²/AWG 5-2
Signal Conductor Cross-Section	0.22 – 2.5 mm²/AWG 24-14
Temperature Range	-40°C up to +125°C

Mechanical Characteristics

Cycle of mechanical operation	≥ 500
Tightening torque power contact screw	6 Nm @ 16 mm² 7 Nm @ 25 mm² 8 Nm @ 35 mm²
Tightening torque signal contact screw	0.8 Nm
Stripping length power contact	13-14 mm
Stripping length signal contact	7.5 mm

Electrical Characteristics

Rated voltage Power, IEC	690 V
Rated Impulse Voltage Power	8 kV
Rated Current Power, IEC	100 A
Contact Resistance Power	≤ 0,5 mΩ
Rated voltage Signal, IEC	400 V
Rated Impulse Voltage Signal	6 kV
Rated Current Signal, IEC	16 A
Contact Resistance Signal	≤ 3 mΩ
Pollution degree Power/Signal	3

381167293	DATA SHEET	
Valid from: 10.07.2025	EPIC® H-K 006/6 MAS	



Materials and Surfaces

Contacts	Copper alloy, hard-silver plated
Insulating Body	PC
Flammability Class according to UL 94	V-0

Standard

Safety Standard	IEC 61984, IEC 60664-1
-----------------	------------------------

Technical Drawings



Pin assignment

381167293	DATA SHEET	
Valid from: 10.07.2025	EPIC® H-K 006/6 MAS	



Industrial machinery and plant engineering



Temperature-resistant



Robust

Info

Combination Insert Power/Signal

Application range

Machine building, Mechanical engineering, renewable energy, plastic industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: TODV1/BU EPIC Released: THBO1/BU EPIC	Document: DB381167293EN Version: 00	Page 3 of 3
---	--	-------------