#### 2170226

# **DATA SHEET**


Valid from: 06.07.2018

UNITRONIC® BUS PB H 7-W 1x2x0.64



## Description

**UNITRONIC® BUS PB H 7-W 1x2x0.64** is a halogen free data cable which is intended for field bus systems such as PROFIBUS or other high performance data networks with 150 Ohms nominal impedance. The cable is intended for limited flexible use and for permanent installation in dry and damp interiors. Due to it's double screening it is suitable for installation in electromagnetically demanding areas.



### **General characteristics**

Conductor flexible bare copper wires,

 $0.22 mm^2 \ or \ 0.64 mm \emptyset$ 

AWG 24/7 foam-skin PE

Insulation foam-skin P
Core identification code Green, Red

Stranding cores stranded with fillers to bundle

Wrapping Polyester tape

Screening aluminum laminated polyester foil

above:

braiding of tinned copper wires

Outer sheath LSZH compound

outer Ø: approx. 7.8 mm

color: violett, similar to RAL 4001

### Mechanical characteristics

Flame propagation

Minimum bending radius flexible:  $9 \times \text{cable } \emptyset$ 

fixed installation: 6 x cable Ø

Permissible temperature range flexible: -5 °C up to +50 °C

fixed installation: -40 °C up to +80 °C flame retardant acc. to IEC 60332-1-2

Halogen free acc. to IEC 60754-1

Low Smoke acc. to IEC 61034

Creator: TOST/PDC	Document: DB2170226EN	Page 1 of 2
Released: ALTE/PDC	Version: 04	

### 2170226

# **DATA SHEET**

Valid from: 06.07.2018

# UNITRONIC® BUS PB H 7-W 1x2x0.64



### **Electrical characteristics**

DC-Resistance (loop)
Insulation resistance
Mutual capacitance

Characteristic impedance

Operating peak voltage velocity of propagation

Test voltage

max. 186.0  $\Omega$ /km min. 5 G $\Omega$  x km nom. 28 nF/km

nom. 270  $\Omega$  (±10%) @9.6 kHz nom. 185  $\Omega$  (±10%) @38.4 kHz nom. 150  $\Omega$  (±10%) (3/20MHz) 250 V (not for power purposes)

approx. 0.81 c

core / core: 1500 V core / screen: 1500 V

## **Transmission properties**

Transmission properties acc. to following specification:

f [MHz]	Attenuation [dB/100m]	
	nominal	
0.0096	0.3	
0.0384	0.4	
4	2.5	
16	4.9	

# Standard

**EU-Directive** 

Dangerous and forbidden substances acc. to RoHS directive (2011/65/EU) are not allowed to the manufacturing.