Valid from: 17.09.2018

EPIC[®] H-B 24 AG-LB



Description

Ideal for many applications due to a wide range of housings and inserts



General Characteristics

Series Version Locking Protection (DIN EN 60529) Protection (NEMA 250, UL50E) Temperature Range	H-B 24 Panel mount base Single lever IP 65 (latched) 12 (latched) -40°C to +100°C, short term up to +125°C		
Materials and Surfaces			
Housing Bolts Lever Sealing	Aluminium alloy, powder-coated, grey Heat-treatable steel, zinc-plated Steel, zinc-plated NBR		
Approvals			
VDE-Approval, VDE-REGNr.	B437		
Standard			
Safety Standard	IEC 61984		

	Creator: MANA2/PDP	Document: DB10102900EN	Page 1 of 2	
	Released: IVSE1/PDP	Version: 01		
We reserve all rights according to DIN ISO 16016				






Valid from: 17.09.2018

EPIC[®] H-B 24 AG-LB

Technical Drawings









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info Universal, robust metal housings size H-B 24

Application range

Plant engineering Light & sound technology Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

	Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB10102900EN Version: 01	Page 2 of 2	
We reserve all rights according to DIN ISO 16016.				