Valid from: 01.04.2019



Application

The compensating cable KN 92 L $2 \times 0.75 \text{ mm}^2$ is a PVC insulated cable which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry and damp rooms. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor	0.75 mm² (24 x 0.20 mm)		
Conductor material	KCA alloying, accuracy cl Positive conductor: Negative conductor:	ass 2 according IEC 60584 Fe (iron) CuNi (cupronickel)	
Core insulation	PVC compound		
Core identification	Positive conductor: Negative conductor:	green white	
Core layering	Cores twisted together		
Outer sheath	PVC compound, colour:	green	
Electrical properties			
Limiting deviation class 2	$\pm 100 \; \mu V \; (\pm 2.5 \; ^\circ C)$ / measuring point temperature +900 $^\circ C$		

Mechanical and thermal properties

Temperature range	occasional flexing:	-5 °C up to +70 °C
Minimum bending radius	occasional flexing:	12 x cable diameter
Flammability	flame retardant in acc. to	IEC 60332-1-2 resp. VDE 0482-332-1-2

Creator: TOME/PCM	Document: DB0162045EN	Page 1 of 1
Released: ALTE/PDC	Version: 02	Page 1 of 1