7038897

DATA SHEET

valid from: 01.01.2019

UNITRONIC® ROBUST S/A FD



Application

UNITRONIC® ROBUST S/A FD are halogen free, robust and high flexible data cables for low frequency applications with outstanding weather, ozone and UV resistance. The cables are among others designed for dry, humid and wet conditions. Considering the temperature range, an outdoor use is possible. At room temperature they are increased resistant to acids, caustic solutions and certain oils. They are especially designed for applications in power chains, automatic manipulators and in permanently moved machine parts.

Design

Design Design based on standard VDE 0812 Conductor superfine wire strands of bare copper wires

Insulation special Polyolefin-based compound

Core identification code according to EN 60947-5-2 3-core: brown, blue, black

4-core: brown, white, blue, black 5-core: brown, white, blue, black, grey

Stranding cores stranded in layers, wrapping with fleece on the outer layer

special halogen free TPE-V compound Outer sheath

colour: black (similar RAL 9005)

Diameter of the outer sheath

Article number	Dimension	Outer sheath ∅
7038897	4x0.25 mm ²	ca. 4.9 mm
7038895	3x0.34 mm ²	ca. 5.0 mm
7038894	4x0.34 mm ²	ca. 5.4 mm
7038896	5x0.34 mm²	ca. 5.9 mm

Electrical properties at 20°C

Conductor resistance 0.25 mm²: max. 79 Ω/km

0.34 mm²: max. 57 Ω/km

Specific volume resistivity > 20 G Ω x cm

Mutual capacitance C/C: approx. 60 nF/km

(at 800 Hz)

Inductance approx. 0.65 mH/km

Peak operating voltage 300 V (not for power applications)

Test voltage C/C: 1500 V

Mechanical and thermal properties

Minimum bending radius Flexing: 5 x cable Ø

Fixed installation: 3 x cable Ø Flexing: - 40°C up to +90°C

Temperature range Fixed installation: - 50°C up to +90°C

Number of cycles max. 10 mio. cycles

Travel distance up to 10 m

Torsional stress max. 3 million cycles at ± 360 °C/meter (not suitable for festoon-applications)

Flammability not flame retardant

Halogen free according to IEC 60754-1 and EN 50267-2-1 Corrosivity of gases according to IEC 60754-2 and EN 50267-2-2

Toxicity according to EN 50305

UV resistance acc. to EN 50525-1 (VDE 0285-525-1) are cables with black sheath suitable for a permanent

outdoor use

acc. to EN ISO 4892-2-2013, method A (change of colour allowed)

Ozone resistance according to EN 50396 resp. VDE 0473-396, method B

according to IEC 60811-404 Oil resistance

This cable is conform to the EU-Directive 2011/65/EU General requirements

(RoHS, Restriction of the use of certain hazardous substances).

Document: DB7038897EN Creator: PESA / PDC Page 1 of 1 Version: Released: ALTE / PDC