



381166840	DATA SHEET	
Valid from: 31.10.2024	EPIC H-BE 024 FQL / H-BE 024 MQL	

Description

- Inserts of the EPIC® H-BE series are considered classics in industry and are ideal for use at higher voltages and currents.
- In the EPIC® H-BE series, inserts of different connection types can be combined with each other as required within the same size (screw, crimp, cage clamp or push-in).
- Push-in connection allows the shortest connection times: strands with wire end ferrules can be inserted and contacted completely without tools; to release the contact, simply press the orange button. For strands without wire end ferrules, the button must be pressed to open the spring before insertion or removal
- The round test socket for 2mm standard test probes is positioned so that it is still accessible for a signal test even when the insert is already installed in the panel-mounting housing.
- Wide variety of suitable housing variations



Pin MQL



Socket FQL



Termination


General Characteristics

Series	H-BE 24
Size	24B
Version	Male/Female (Article 381166841/381166840)
Number of Contacts	24+PE
Termination Methods	Push-In Termination: 0.5 - 2.5 mm ² (AWG 26 - 14)
Stripping Length	8-10 mm
Temperature Range	-40°C to +125°C

Mechanical Characteristics

Cycle of mechanical operation	> 500
-------------------------------	-------

Creator: THB01/BU-EPIC Released: TODV1/BU-EPIC	Document: DB381166840EN Version: 00	Page 1 of 3
---	--	-------------

381166840	DATA SHEET	
Valid from: 31.10.2024	EPIC H-BE 024 FQL / H-BE 024 MQL	

Electrical Characteristics

Rated Voltage, IEC	500 V
Rated Voltage, UL/CSA	600 V
Rated Impulse Voltage	6 kV
Rated Current, IEC	16 A
Contact Resistance	≤ 1 mΩ
Degree of Soiling	3

Materials and Surfaces

Contacts	Copper alloy, hard silver-plated
Insulating Body	Polycarbonate
Flammability Class according to UL 94	V0


Approvals

UL-Approval, E-File-Number	E75770
----------------------------	--------


Standard

Safety Standard	IEC 61984, UL 1977
-----------------	--------------------

Technical Drawings




Technical Drawing and Polar Pattern female FCC



Technical Drawing and Polar Pattern male FCC



381166840	DATA SHEET	
Valid from: 31.10.2024	EPIC H-BE 024 FQL / H-BE 024 MQL	



Robust



Temperature resistant

Info

Multifunctional insert for versatile applications
Screw, crimp, cage clamp and Push-In version - freely combinable

Application range

Mechanical engineering
Light & sound technology
Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: THB01/BU-EPIC Released: TODV1/BU-EPIC	Document: DB381166840EN Version: 00	Page 3 of 3
---	--	-------------