


381167597	<b>DATA SHEET</b>	
Valid from: 28.03.2025	<b>EPIC® H-Q MTG</b>	

## Description

- The hood can be connected with many standard housings (mount base, surface-mount base or cable coupler housings).
- With space-saving female thread for use with metric cables or conduit glands.
- Locking takes place using a central lever on the counter-housing.
- Meets protection class IP 65 when locked.
- Article names with the suffix "EMC" are specially designed for environments in which electromagnetic compatibility (EMC) is required.
- Withstands high environmental and mechanical stress.



## General Characteristics

Series	H-Q
Version	Hood
Locking	Pins for single lever
Cable entry	Top
Protection (DIN EN 60529)	IP 65 (latched)
Temperature Range	-40°C to +125°C

## Materials / Surfaces

Housing	Zinc die-cast
Surface	See table

## Standard

Safety Standard	IEC 61984
-----------------	-----------


## Versions

Article number	Article description	Surface
381167597	EPIC® H-Q MTG PE M25 BK	Powder-coated, black
381167599	EPIC® H-Q MTG PE M25 EMC	Nickel plated

Creator: TODV1/BU EPIC Released: FICE1/BU EPIC	Document: DB381167597EN Version: 01	Page 1 of 2
---	--	-------------

381167597	<b>DATA SHEET</b>	
Valid from: 28.03.2025	EPIC® H-Q MTG	

## Technical Drawings



UV-resistant



Halogen free



Heat-resistant



Cold-resistant



Interference signal (EMC version)

## Application range

For connecting devices and machines to a power supply in various applications. Typical areas of application are electric motors and servo drives.

## Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: TODV1/BU EPIC Released: FICE1/BU EPIC	Document: DB381167597EN Version: 01	Page 2 of 2
---	--	-------------