


381167280	DATA SHEET	
Valid from: 09.07.2025	EPIC® H-K 004.2/4 MAS 14-22	

Description

- Combination insert Power and Signal
- High power in one connector insert
- Best in combination with ÖLFLEX® SERVO
- Axial-Screw termination



Images may vary

General Characteristics

Series	H-K 4.2/4
Version	Male
Design Size	10B
Number of Contacts	8 + PE
Number of Power Contacts	4
Number of Signal Contacts	4
Termination Method Power	Axial screw termination: 10-22 mm ² /AWG 8-4
Termination Method Signal	Cage spring termination: 0.14-2.5 mm ² /AWG 26-14
Temperature Range	-40°C up to +125°C

Mechanical Characteristics

Cycle of mechanical operation	≥ 500
Tightening torque power contact screw	4 Nm @ 16 mm ² 5 Nm @ 22 mm ²
Stripping length power connection	11-12 mm @ 16 mm ² 13-14 mm @ 22 mm ²
Stripping length signal connection	7-9 mm

Electrical Characteristics

Rated voltage Power, IEC	690 V
Rated Impulse Voltage Power	8 kV
Rated Current Power, IEC	63 A
Contact Resistance Power	≤ 0,5 mΩ
Rated voltage Signal, IEC	250 V
Rated Impulse Voltage Signal	4 kV
Rated Current Signal, IEC	16 A
Contact Resistance Signal	≤ 3 mΩ
Pollution degree Power/Signal	3

Materials and Surfaces

Contacts	Copper alloy, hard-silver plated
Insulating Body	PC
Flammability Class according to UL 94	V-0


Standard

Safety Standard	IEC 61984, IEC 60664-1
-----------------	------------------------

Creator: TODV1/BU EPIC Released: THBO1/BU EPIC	Document: DB381167280EN Version: 00	Page 1 of 3
---	--	-------------

381167280	DATA SHEET	
Valid from: 09.07.2025	EPIC® H-K 004.2/4 MAS 14-22	

Technical Drawings



381167280	DATA SHEET	
Valid from: 09.07.2025	EPIC® H-K 004.2/4 MAS 14-22	



Industrial machinery and plant engineering



Temperature-resistant



Wind Energy

Info

Combination Insert Power

Application range

Plant engineering
Renewable energy
Control engineering

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: TODV1/BU EPIC Released: THBO1/BU EPIC	Document: DB381167280EN Version: 00	Page 3 of 3
---	--	-------------