

## **DATA SHEET**

0161017

IEC extension cable KE 12 L 2x1,5 oval

valid from:

01.12.2008

## **Application**

The extension cable KE 12 L 2 x 1,5 mm<sup>2</sup> is a PVC insulated cable which transmits the thermoelectric voltage of Fe/CuNi thermocouples. It is for flexible use and fixed installation in dry and damp rooms. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

Design

Conductor 1,5 mm<sup>2</sup> (48 x 0,20 mm)

Conductor material JX alloying, accuracy class 2 according IEC 60584

Positive conductor: Fe (iron)

Negative conductor: CuNi (cupronickel)

Core insulation PVC compound

Core identification Positive conductor: black

Negative conductor: white

Core layering Cores parallel next to each other

Outer sheath PVC compound, colour: black

**Electrical properties** 

Limiting deviation class 2 ± 140 µV (± 2,5 ℃) / m easuring point temperature +500 ℃

Mechanical and thermal properties

Temperature range occasional flexing: -5 ℃ up to +70 ℃

Minimum bending radius occasional flexing: 12 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2