# 0162007 DATA SHEET

Valid from: 01.04.2019

## IEC compensating cable KN 4 L-SIL-S 2x1,5 oval



# **Application**

The compensating cable KN 4 L-SIL-S 2 x 1,5 mm² is a silicone insulated cable which transmits the thermo-electric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry rooms with low mechanical load. They may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range. The steel wire armouring serves as mechanical protection.

## Design

Conductor 1.5 mm<sup>2</sup> (48 x 0.20 mm)

Conductor material KCA alloying, accuracy class 2 according IEC 60584

Positive conductor: Fe (iron)

Negative conductor: CuNi (cupronickel)

Core insulation Silicone compound

Core identification Positive conductor: green

Negative conductor: white

Core layering Cores parallel next to each other

Outer sheath Silicone compound, colour: green

Armouring Galvanized steel wire braiding with interweaved, green identification thread

#### **Electrical properties**

#### Mechanical and thermal properties

Temperature range occasional flexing: -25 °C up to +180 °C

Minimum bending radius occasional flexing: 15 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2