#### **DATA SHEET**



## ÖLFLEX® 190 & 190 CY

#### **UDB602002EN**

Date: January 1, 2019

#### 1. APPLICATION

ÖLFLEX<sup>®</sup> 190 is a multi-conductor cable with a highly oil-, coolant-, and solvent-resistant jacket for control and power applications in an industrial environment. It is designed for use in all electrical equipment under dry, damp and wet conditions. ÖLFLEX<sup>®</sup> 190 is also UL TC approved so it can be routed in tray as well. ÖLFLEX<sup>®</sup> 190 CY is a shielded version for EMI and RFI protection.

#### Applications:

CNC machining centers, grinding machines, bottling equipment, conveyors, processing equipment, assembly lines, control panels and can substitute for anywhere that industrial equipment cables are used.

#### **Underwriters Laboratories**

For Tray use in exposed run applications, Wind Turbines, Machine Tools etc. and internal or external wiring of electrical and electronic equipment.

#### Canadian Standards

For Appliance Wiring Material and internal or external wiring of electrical and electronic equipment applications.

#### 2. CABLE DESCRIPTION

- Bare copper fine wire
- PVC insulation
- Black color coded conductors with white identification
- Green/Yellow ground wire
- Gray UV, oil and flame resistant specially formulated Inner PVC jacket
- Overall TC Braid Shield
- Grav (RAL 7001) UV, oil and flame resistant specially formulated thermoplastic polymer jacket

#### 3. TECHNICAL DATA

Conductor Stranding 20 AWG (0,50 mm²) to 6 AWG (16,0 mm²): Class 5 (IEC 60228; VDE 0295)

20 & 18 AWG meets only class 5 cross section and DC conductor resistance

4 AWG (21,0 mm²) to 2 AWG (33,7 mm²): Class K

Design / Make-up Cable is designed in accordance with the requirements of UL Standard 1277

and with CSA standards C22.2 No. 210

Insulation Specially formulated PVC insulation

Color Code Black conductors with white numbers plus green/yellow (30% stripe width)

2 conductor cable: No green/yellow ground

Inner Sheath Specially formulated PVC jacket (ÖLFLEX 190 CY only)

Shield Tinned Copper Braid Shield (85% coverage) (ÖLFLEX 190 CY only)

Outer Sheath Specially formulated thermoplastic polymer jacket

Nominal Voltage UL PLTC (20 AWG Only): 300V

UL TC (18 AWG - 2 AWG): 600V UL WTTC (18 AWG - 2 AWG) / CSA AWM: 1000V VDE U<sub>0</sub>/U: 600/1000V

Engineer: D. Kocheta
Approval: J. Gavilanes

Document: UDB602002EN

Page 1 of 2

Lapp USA

### **DATA SHEET**



# ÖLFLEX® 190 & 190 CY

**UDB602002EN Date:** January 1, 2019

Test Voltage 2000V

Min Bend radius For installation: 4 x OD

Shielded 6 x OD

Temperature Range For stationary use: -40°C to +90°C

For flexible use: -5°C to +90°C

Cable Attributes OR-04, FR-03, WT-02, MP-03

Sunlight resistant, Direct Burial

Approvals UL Type TC (Tray Cable) - ER\* (Exposed Run) per UL 1277

(18 AWG - 2 AWG)

UL WTTC (Wind Turbine Tray Cable) per UL 2277

(18 AWG - 2 AWG)

UL PLTC (Power Limited Tray Cable) -ER\* (Exposed Run) per UL 13

(20 AWG Only)

UL AWM (Appliance Wiring Material) 21098 (Oil), 2587 & 20886 per UL 758

CSA AWM I/II A/B FT4 per CSA C22.2 No. 210
\* For –ER: Minimum 3 conductors required

Additional NEC Article 336, Article 501

NFPA 79

VDE 250-1 (meets rated voltage requirements only)

LVD 2014/35/EU (Low Voltage Directive)

RoHS directive

Engineer: D. Kocheta Approval: J. Gavilanes

Document: UDB602002EN