

381166350	<b>DATA SHEET</b>	
Valid from: 05.11.2024	<b>EPIC® POWER M 12F SCREW 4-pin</b>	

**Description:**

- Circular connectors for power transmission
- Straight version with cable aperture 8 mm - 12 mm
- High-quality gold-plated screw contacts



**Product variants:**

Article number	Type	Pole image	Cable diameter
381166350	Cable plug with male contacts (F6)	F-coded; 4-pin	8 mm - 12 mm
381166351	Cable socket with female contacts (D6)	F-coded; 4-pin	8 mm - 12 mm

**General characteristic:**

Series	Power M12
Coding	F-coded
Type	Cable plug/cable socket, straight
Pole image	4-pole
Rated voltage	63 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Rated current	16 A
Contact resistance	≤ 10 mΩ
Connection cross-section	Screw contacts 0.5 - 2.5 mm²
Cable connection	8 mm - 12 mm
Protection class	IP 67 according to IEC 60529
Mating cycles	> 100
Temperature range	-25°C up to +85°C
Tightening torque Contact	0.3 Nm
Tightening torque cable clamp	0.6 Nm
Tightening torque for connector locking	0.3 Nm

**Materials/surface:**

Contacts	Copper alloy
Contact surface	Au (gold)
Contact body material	PA

**Standards:**

Product standard	DIN EN 61076-2-111
------------------	--------------------

**Approvals:**


In preparation

Creator: VACH1/BU EPIC Released: JUKL2/BU EPIC	Document: DB381166350EN Version: 00	Page 1 from 2
---	--	---------------

381166350	<b>DATA SHEET</b>	
Valid from: 05.11.2024	<b>EPIC® POWER M 12F SCREW 4-pin</b>	


Technical drawings

Technical drawing




Cable plug F6

Pole image




Technical drawing



Cable socket D6

Pole image



Assembly:

Sheath length:	25 - 30 mm
Stripping length:	4 - 5 mm
Tightening torque Contact:	0.3 Nm
Tightening torque cable clamp:	0.6 Nm

Areas of application:

Power transmission for mechanical and plant engineering and servomotors

Note:

The photographs are not to scale and are not detailed images of the respective products.  
Further information can be found in the product standard.