


21700640	DATA SHEET	
Valid from: 07.07.2020	ED-IE-90-6A-B-20-FD-FC	

Product description

- Field mountable Industrial Ethernet RJ45 connector with colour coding according to T568B
- Cable outlet in 4 different 90°-steps modifiable
- Suitable for industrial applications, data centres and home networks
- Especially designed for cables with a core diameter of AWG24-27/7 and high flexible cables with a core diameter of AWG26/19 such as ETHERLINE® drag chain cable of the Lapp Group (e.g. 2170488)



General properties

Ambient temperature	-40 to +85 °C
Protection degree	IP 20
Outer diameter, cable	5,5 – 10,0 mm
Outer diameter, wire	0,85 – 1,1 mm
Termination cross section, stranded, 7 wires	AWG27/7 – AWG24/7
Termination cross section, stranded, 19 wires	AWG26/19
Termination cross section, solid	AWG26/1 – AWG24/1
Cable outlet, variable	0°, 90°, 180°, 270°

Mechanical properties

Insertion force	≤ 30 N
Mating cycles	≥ 750
Cable extraction force (assembled connector)	≥ 50 N

Electrical properties

Contact resistance	≤ 20 mΩ
Insulation resistance	≥ 500 MΩ
Proof voltage, contact-contact	≥ 1000 V, DC
Proof voltage, contact-shield	≥ 1500 V, DC
Current carrying capacity at 50 °C	1 A
Suitable for Power over Ethernet+ acc. to IEEE 802.3at	yes


Transmission properties

Suitable for 10 Gigabit Ethernet acc. to IEEE 802.3an	yes
Category 6 _A	ISO/IEC 11801; DIN EN 50173-1
Class E _A	ISO/IEC 11801; DIN EN 50173-1
Category 6A	ANSI/TIA/EIA-568-C.2

Materials

Inflammability class in according to UL94	V0
Connector housing, base material	die-cast zinc
Connector housing, surface	Ni
Contacts, surface	Au

Creator: MANA2/PDP	Document: DB21700640EN	Page 1 of 2
Released: IVSE1/PDP	Version: 03	

21700640	DATA SHEET	
Valid from: 07.07.2020	ED-IE-90-6A-B-20-FD-FC	

Approvals

UL listed, E-File

E353543

Standards

Product standard

RJ45 connector acc. to IEC 60603-7-51






ANSI/TIA/EIA-568-C.2

Generic cable systems

ISO/IEC 11801

DIN EN 50173-1

Drawings



Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB21700640EN Version: 03	Page 2 of 2
---	---------------------------------------	-------------