# 0152017 DATA SHEET

Valid from: 01.04.2019

## DIN compensating cable KN 12 L 2x1,5 oval



## **Application**

The compensating cable KN 12 L 2 x 1,5 mm² is a PVC insulated cable which transmits the thermoelectric voltage of NiCr/Ni thermocouples. It is for flexible use and fixed installation in dry and damp rooms. They may only be installed outdoors with UV protection and in observation of the max. permitted temperature range.

### Design

Conductor 1.5 mm<sup>2</sup> (48 x 0.20 mm)

Conductor material KCA alloying, accuracy class 2 according DIN 43722

Positive conductor: Fe (iron)

Negative conductor: CuNi (cupronickel)

Core insulation PVC compound

Core identification Positive conductor: red

Negative conductor: green

Core layering Cores parallel next to each other

Outer sheath PVC compound, colour: green

#### **Electrical properties**

Limiting deviation class 2 ±100 µV (±2.5 °C) / measuring point temperature +900 °C

## Mechanical and thermal properties

Temperature range occasional flexing: -5 °C up to +70 °C

Minimum bending radius occasional flexing: 12 x cable diameter

Flammability flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2