# DATA SHEET

valid from: 28.09.2021 H05Z-K 90°C



### **Application**

4725001

H05Z-K is a halogen-free, low smoke cable with cross-linked insulation and low emission of corrosive gases. For internal wiring of machine tools, for wiring of lamps and especially for applications where low smoke density and low emission of corrosive gases are required in case of fire.

Application range:

Suitability for the laying inside of conduits installed on or under plaster in case of signal and control current circuits only.

### Design

Design acc. to EN 50525-3-41

CertificationThe cable is marked with the ⊲HAR⊳ HAR-sign or HAR-identification thread.Conductorfine-wire copper conductor acc. to IEC 60228 resp. EN 60228, class 5Insulationhalogen-free, cross-linked compound EI 5 acc. to EN 50363-5

Core identification code different colours

## Electrical properties at 20 °C

Nominal voltage  $U_0/U$ : 300/500 V Test voltage 2000 V AC

#### Mechanical and thermal properties

Minimum bending radius at intended use: 4 x outer diameter

at cautious bending: 2 x outer diameter

Temperature range Fixed installation: -40°C to +90°C

During installation: -5 °C to +90 °C

Flammability acc. to IEC 60332-1-2 resp. EN 60332-1-2
Halogen free acc. to EN 50525-1, appendix B; EN 60754-1
Corrosivity of gases acc. to IEC EN 60754-2 resp. EN 60754-2

Smoke density acc. to EN 61034-2

Tests acc. to IEC 60811 resp. EN 60811, EN 50395 and EN 50396

General requirements These cables are conform to the EU Directive 2014/35/EU (Low Voltage Directive)

Environmental information These cables meet the substance-specific requirements of the EU Directive 2011/65/EU (RoHS).

Note Trade product, no Lapp product