

Ethernet Switch 16-port, unmanaged, 10/100 Mbps (ETHERLINE[®] ACCESS UF16T)



Application area

The LAPP Ethernet Switch 16-port unmanaged is suitable for installation on a DIN rail and connects up to 16 Ethernet participants with 10 or 100 Mbps.

Connections

The Ethernet Switch 16-port has 16 RJ45 connections. The Ethernet Switch 16-port must be supplied with 24 V DC at the 18 - 30 wide range input via the provided connector plug. The terminal (FG) is for the functional ground. Connect this correctly with the reference potential.

Features

- Store-and-Forward architecture
- 10Base-T/100Base-TX
- Full-/Half-Duplex
- Auto negotiation
- Auto MDI/MDI-X (IEEE 802.3u Auto crossover support)
- QoS-Priority-Queues: 8
- LLDP & PTCP Delay-Traffic blocking (for PROFINET)
- 2x 16K MAC address lookup table
- 2x 256 Kbyte memory for frame buffering
- IEEE 802.3x Full duplex flow control
- Up to 51 Gbps high-performance memory bandwidth
- Support Jumbo frame sizes up to 10KByte

LEDs

PWR Led	On = Power supply present
	Off = No voltage or the device is defective

RJ45 LEDs

Orange (Link/Activity):	On = Connected	Blinks = Data transmission
Green (Speed):	On = 100 Mbps	Off = 10 Mbps



Technical data

Order no.	ETHERLINE [®] ACCESS UF16T	
Name	Ethernet Switch 16-Port, unmanaged 10/100 Mbps for DIN rail	
General information		
- Scope of delivery	Ethernet 16-port switch with power supply plug, short manual	
- Dimensions (DxWxH)	32 x 123 x 76 mm	
- Weight	approx. 270g	
LAN interface		
- Number	16	
- Туре	10/100Base-T/TX, Full/Half-Duplex, Auto negotiation, Auto MDI/MDI-X; IEEE Auto crossover	
- Connection	RJ45	
- Transmission rate	10/100 Mbps	
Status indicator	1 LEDs power display, 32 LEDs Ethernet status	
Voltage supply	24 V DC (1830 V DC)	
Current draw	max. 160 mA with 24 V DC	
Power loss	3,7 W	
Environment requirements		
- Ambient temperature	-25 °C +75 °C	
 Transport and storage temperature 	-40 °C +85 °C	
 Relative air humidity 	95 % r H without condensation	
 Pollution degree 	2	
 Protection rating 	IP20	
- Certifications	CE	
UL	UL 61010-1/ UL 61010-2-201	
 Voltage supply 	DC 24 V (18 30 VDC, SELV and limited energy circuit)	
- Pollution degree	2	
- Altitude	Up to 2000 m	
 Temperature cable rating 	87 °C	

Note:

The contents of this document have been checked by us for matching with the hardware and software described. However, we assume no liability for any existing differences, as these cannot be fully ruled out.

The information in this document is, however, updated on a regular basis. When using your purchased products, please make sure to use the latest version of the document, which can be viewed and downloaded in the Internet at

https://www.lappkabel.com/activenetworkcomponents.

Version: 1 - 2019-11-14 for HW 1